

HUBBELL
Wiring Device-Kellems

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female, Mechanically Interlocked Receptacle, 100A 3-Phase Delta 250V AC,

By Hubbell Wiring Device-Kellems
Catalog # [HBL4100MI9WR](#)

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female, Mechanically Interlocked Receptacle, 100A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, Terminal Screws



Application

- High Ampacity Watertight Connections

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current and voltage
- Electrical - Dielectric Voltage - Withstands 3,000V AC Min
- Electrical - Max. Working Voltage - 600V AC RMS
- Environmental - Flammability - UL94-5VA and V-0 Classification
- Environmental - Ingress Protection - IP67 Suitability
- Environmental - Moisture Resistance - Outdoor - 4X (Watertight, Washdown)
- Indoor - 12 (Dust-tight, Falling Dirt and Noncorrosive Liquids).
- Environmental - Operating Temperature - Max. Continuous +75°C
- Min. Continuous -40°C
- Mechanical - Impact Resistance - In accordance with UL 746C
- Mechanical - Mounting - External adjustable feet
- Mechanical - Product Identification - Identification and ratings are part of the external label and molded into the receptacle mount
- Mechanical - Terminal Identification - In accordance with UL, CSA and international conventions

General

| | |
|------------------------------|--|
| Catalog Number | HBL4100MI9WR |
| Color | Blue |
| EU RoHS Indicator | No |
| Environmental Conditions | Watertight |
| Item Type | Mechanically Interlocked Single, Reversed |
| Material | Thermoplastic |
| Material - Mounting Hardware | Screw Mounting |
| Number Of Poles | 3-Pole |
| Series | Non-Fused |

Specifications

Style
Type
UPC

- Base - Valox®
 - Conduit Hub - Zinc
 - Enclosure Gasket - Neoprene
 - Face - Valox®
 - Shaft Seal - Neoprene
- Reverse Service
Mechanical Interlock
783585012681

Dimensions

Display Size Standard Sized Product

Electrical Ratings

| | |
|----------------------------|--------------------------|
| Amperage Rating | 100 A |
| Connectivity | Pressure Terminal Screws |
| Current / Amperage Rating | 100 A |
| Current Rating | 100 A |
| Phase | Three Phase |
| Voltage Rating | 3 Phase 240 VAC |
| Voltage Rating Description | 3 Phase 240 VAC |
| Wattage | 25000 |

Conductor Related

| | |
|-----------------|--------------------|
| Number Of Wires | 4-Wire |
| Wire Size | #3 AWG to #1/0 AWG |

Certifications And Compliance

| | |
|----------------------|-----------|
| Industry Standard(s) | UL Listed |
| Nema Rating | Non-NEMA |

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Specifications - HBL4100MI9WR](#)
- [Warranty - Industrial & Commercial Products](#)

