

# Straight Blade Devices, Female Connector Body, Valise Series, Industrial/Commercial Grade, Straight, 2-Pole 3- Wire Grounding, 20A 125V, 5-20R

By Hubbell Wiring Device-Kellems  
Catalog # [HBL5369VY](#)



Straight Blade Devices, Female Connector Body, Valise Series, Industrial/Commercial Grade, Straight, 2-Pole 3- Wire Grounding, 20A 125V, 5-20R, Yellow, Single Pack.

## Application

- Industrial/Commercial

## Performance

- Electrical:Current Interrupting: Certified for current interrupting at full rated current
- Dielectric Voltage: Withstands 2,000V minimum
- Mechanical :Terminal Accommodation #18-#12 AWG stranded copper wire only
- Terminal Identification: Terminals identified in accordance with UL 498 and CSA
- Environmental :Flammability: UL 94 HB or better
- IP Suitability: IP20
- Operating Temperatures: Maximum continuous 75°C
- minimum -40°C (w/o impact)

## General

Catalog Number	HBL5369VY
Color	Yellow
Cord Range	0.300"-0.660" (7.6-16.8)
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	1
Insulation	Insulated Body
Item Type	Valise
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Valise®
Specifications	<ul style="list-style-type: none"><li>• Assembly Screws - Plated Steel</li><li>• Assembly Screws - Plated steel</li><li>• Cable Inserts - PPO</li><li>• Contacts - Brass</li></ul>

- Housing - Nylon
- Terminal Clamp - Nickel plated steel
- Terminal Screws - #8-32 Brass , multiple drive

## Style

Temperature Rating

## Type

UPC

Standard

Max Continuous- 75 Degrees C, Minimum- -40 Without Impact

Connector Body

783585013176

## Dimensions

Dimensions	2.68 in x 1.32 in x 2.68 in
Display Size	Standard
Height	2.68 in
Length	2.68 in
Weight	0.15 lb
Width	1.32 in

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Screw Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V

## Conductor Related

Conductor Range	#18 AWG to #12 AWG
Number Of Wires	3-Wire
Number of Conductors	3-Wire
Wire Size	#18 AWG to #12 AWG

## Certifications And Compliance

Industry Standard(s)

- CSA Certified to C22.2 No. 42 File 280C
- NEMA® WD-6 Compliant
- UL Listed to UL498 File E1706

Nema Rating

5-20R

Standards - RoHS Compliance

CM

Status

## Logistics

Carton Quantity

10

Pallet Quantity

6000

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)

[Specifications - HBL5369VY](#)

[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK\_MX-HBL5369VY-SPEC-EN | REV 10/2024