



Straight Blade Devices, Inlets, Flanged, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, Stainless, Single Pack

By Hubbell Wiring Device-Kellems
 Catalog # [HBL5379C](#)



Straight Blade Devices, Inlets, Flanged, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, Stainless, Single Pack.

Features

- Impact resistant thermoplastic construction
- Backwired terminations for ease of installation
- #8-32 Multiple drive terminal screws
- Mounting screws included

Application

Heavy Duty

General

Color	White
Cord Range	0.230"-0.720" (5.8-18.3)
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	1
Item Type	Flanged Single
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 V-2
- Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #18-#10 AWG copper stranded or solid conductor only

Dimensions

Dimensions	1.71 in x 1.69 in x 1.71 in
Display Size	Standard Sized Product
Height	1.71 in
Length	1.71 in
Weight	0.15 lb
Width	1.69 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V
Wattage	2500 W

Conductor Related

Conductor Range	#18 AWG to #10 AWG
Number Of Conductors	3-Wire
Number Of Wires	3-Wire
Wire Size	#18 AWG to #12 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA, C22.2, No. 42 • NEMA® WD-6 Compliant • UL Listed, File E2186
----------------------	--

Nema Rating	5-20R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2023](#)
[Warranty - Industrial & Commercial Products](#)

- Solid conductor only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

Series	Extra Heavy Duty
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact
Type	Flanged Receptacle
UPC	783585174457



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_MX-HBL5379C-SPEC-EN | REV 1/2024