

## Straight Blade Devices, Receptacles, Combo Duplex, Industrial Grade, 2-Pole 3-Wire Grounding, 20A 250V, 6- 20R, Brown, Single Pack

By Hubbell Wiring Device-Kellems  
Catalog # [HBL5492](#)



Straight Blade Devices, Receptacles, Combo Duplex, Industrial Grade, 2-Pole 3-Wire Grounding, 20A 250V, 6- 20R, Brown, Single Pack.

### Features

- Receptacles
- Combo Duplex
- Industrial Grade
- 2-Pole 3-Wire Grounding

### Application

Heavy Duty

### Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 V-2 or better
- Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

### General

|                              |  |
|------------------------------|--|
| Catalog Number               | HBL5492  |
| Color                        | Brown  |
| EU RoHS Indicator            | Yes  |
| Environmental Conditions     | Indoor Dry Unless Protected By Additional Means          |
| Horsepower - Maximum         | 2  |
| Item Type                    | Combination Duplex Receptacles                           |
| Material - Mounting Hardware | Screw Mounting   |
| Number Of Poles              | 2-Pole   |
| Operating Temperature        | Maximum continuous 75°C and minimum -40°C without Impact |
| Series                       | Extra Heavy Duty   |

### Specifications

Style  
Type  
UPC

- Base - Reinforced PET
  - Face - Nylon
  - Power Contacts - .037" (.9) Brass
- Finder Groove Face  
Combination Receptacle  
783585435442

### Dimensions

|              |                            |
|--------------|----------------------------|
| Dimensions   | 3.28 in x 1.5 in x 0.88 in |
| Display Size | Standard Sized Product     |
| Height       | 0.88 in                    |
| Length       | 3.28 in                    |
| Weight       | 0.25 lb                    |
| Width        | 1.5 in                     |

### Electrical Ratings

|                            |                           |
|----------------------------|---------------------------|
| Amperage Rating            | 20 A                      |
| Connectivity               | Back and Side Wired       |
| Current / Amperage Rating  | 20 A                      |
| Current Rating             | 20 A                      |
| Dielectric Strength        | Withstands 2,000V minimum |
| Phase                      | Single Phase              |
| Voltage Rating             | 125/250 V                 |
| Voltage Rating Description | 125 V;250 V               |
| Wattage                    | 5000 W                    |

### Conductor Related

|                 |                    |
|-----------------|--------------------|
| Number Of Wires | 3-Wire             |
| Wire Size       | #14 AWG to #10 AWG |

### Certifications And Compliance

|                      |  |
|----------------------|--|
| Industry Standard(s) | <ul style="list-style-type: none"><li>• Certified to CSA, C22.2, No. 42 File 285</li><li>• UL Listed to UL498 File E2186</li></ul> |
| Nema Rating          | 5-20R, 6-20R   |

Standards - RoHS Compliance CM  
Status

**Logistics**

Carton Quantity 10

**Product Assets**

[Catalogs - WDK Catalog Full 2024](#)

[Specifications - HBL5492](#)

[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved  
WDK\_MX-HBL5492-SPEC-EN | REV 1/2025