

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male, Plug, 60A 3-Phase Wye 120/208V AC, 4- Pole 5-Wire Grounding, Watertight



By Hubbell Wiring Device-Kellems
Catalog # [HBL560P9W](#)

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male, Plug, 60A 3-Phase Wye 120/208V AC, 4- Pole 5-Wire Grounding, Terminal Screws, Blue, Watertight

Application

- High Ampacity Connections

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 3,000V AC Min
- Electrical - Max. Working Voltage - 600V AC RMS
- Environmental - Flammability - HB or Better per UL 94 or CSA C22.2 No. 0.17
- Environmental - Ingress Protection - IP67 Suitability
- Environmental - Moisture Resistance - Watertight per IEC 60309-1
- Environmental - Operating Temperature - Maximum Continuous 75°C
- Minimum - 40°C w/o impact
- Mechanical - Impact Resistance - Per CSA C22.2 No. 182.1 / UL1682
- Mechanical - Product Identification - Identification and ratings are a permanent part of the device housing.
- Mechanical - Terminal Identification - Terminals identified in accordance with North American and IEC conventions

General

Catalog Number	HBL560P9W
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Item Type	Male Plug
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	4-Pole
Series	HBL Heavy Duty
Specifications	<ul style="list-style-type: none">• Contact Carrier - High-Impact Thermoset• Housing - Zytel® ST801 Nylon• Locking Ring - Reinforced Thermoplastic Polyester

Style
Type
UPC

• Retainer - High-Impact Thermoset
• Terminal Screws - Stainless Steel
Standard Service
Watertight Plug
783585405704

Dimensions

Display Size Standard Sized

Electrical Ratings

Amperage Rating 60 A
Connectivity Pressure Terminal Screws
Current / Amperage Rating 60 A
Current Rating 60 A
Phase Three Phase
Voltage Rating 3 Phase Y 120/208 VAC
Voltage Rating Description 3-Phase 120/208 VAC

Conductor Related

Cord Type All Portable
Wire Size #8 AWG to #2 AWG

Certifications And Compliance

Industry Standard(s)
Nema Rating

- CSA Standard C22.2 No. 182.1
- UL Classified to IEC60309-1
- UL Listed, File E146032

Non-NEMA

Logistics

Carton Quantity 10
Pallet Quantity 180

Product Assets



A Hubbell brand