



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female, Connector Body, 30A 3-Phase Delta 250V AC, Watertight

By Hubbell Wiring Device-Kellems
Catalog # [HBL430C9W](#)



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female, Connector Body, 30A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, Terminal Screws, Blue, Watertight

Features

- Insulated Non-Metallic housing
- Color coded housings by voltage for easy identification
- Corrosion-resistant self-closing gasketed cover

Application

High Ampacity Connections

General

Color	<ul style="list-style-type: none"> • Blue • Bleu
Environmental Conditions	Watertight
Insulation	Insulated Body
Item Type	Standard
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - 3000V AC • Electrical - Max. Working Voltage - 600V RMS • Environmental - Flammability - HB or better per UL 94 or CSA C22.2 No. 0.17 • Environmental - Ingress Protection - IP67 Suitability • Environmental - Moisture Resistance - Watertight per IEC 60309-1 • Environmental - Operating Temperatures - Maximum Continuous 75°C • Minimum - 40°C w/o impact • Mechanical - Impact Resistance - Per CSA C22.2 No.182.1 /UL1682 • Mechanical - Product

Dimensions

Display Size Standard

Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Voltage Rating	3 Phase 250 VAC
Voltage Rating Description	3 Phase 250 VAC

Conductor Related

Conductor Range	#12 AWG to #8 AWG
Number Of Conductors	4-Wire Grounding
Number Of Wires	4-Wire

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • CSA Certified File LR280C • UL Classified to IEC 60309-1 IEC 60309-2 • UL Listed, File E146033
----------------------	--

Nema Rating Non-NEMA

Logistics

Carton Quantity 10

Product Assets

[Catalogs - WDK Catalog Full 2023](#)
[Warranty - Industrial & Commercial Products](#)

Mechanical - Product Identification - Identification and ratings are a permanent part of the device housing

- Mechanical - Terminal Identification - Terminals identified in accordance with North American and IEC conventions

Series	HBL Heavy Duty
Style	Standard Service
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	<ul style="list-style-type: none">• Watertight Connector Body• Watertight Connector Body
UPC	783585404547



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_MX-HBL430C9W-SPEC-EN | REV 1/2024