

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male, Plug, 30A 125/250V, 3-Pole 4-Wire Grounding, Terminal Screws, Watertight

By Hubbell Wiring Device-Kellems
Catalog # [HBL430P9WR](#)

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male, Plug, 30A 125/250V, 3-Pole 4-Wire Grounding, Terminal Screws, Orange, Watertight



Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 3,000V AC Min
- Electrical - Max. Working Voltage - 600V AC RMS
- Environmental - Flammability - HB or Better per UL 94 or CSA C22.2 No. 0.17
- Environmental - Ingress Protection - IP67 Suitability
- Environmental - Moisture Resistance - Watertight per IEC 60309-1
- Environmental - Operating Temperature - Maximum Continuous 75°C
- Minimum - 40°C w/o impact
- Mechanical - Impact Resistance - Per CSA C22.2 No. 182.1 / UL1682
- Mechanical - Product Identification - Identification and ratings are a permanent part of the device housing.
- Mechanical - Terminal Identification - Terminals identified in accordance with North American and IEC conventions

General

Catalog Number	HBL430P9WR
Color	Blue
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Item Type	Male Plug- Reversed
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
Series	Non-Fused
Specifications	<ul style="list-style-type: none"> • Contact Carrier - High-Impact Thermoset • Housing - Zytel® ST801 Nylon • Locking Ring - Reinforced Thermoplastic Polyester • Retainer - High-Impact Thermoset

Style
Type
UPC

- Terminal Screws - Stainless Steel
- Reverse Service
- Watertight Mating Plug
- 783585012711

Dimensions

Display Size Standard Sized

Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Phase	Three Phase
Voltage Rating	3 Phase 240 VAC
Voltage Rating Description	3 Phase 240 VAC

Conductor Related

Cord Type	All Portable
Number Of Wires	4-Wire
Wire Size	#12 AWG to #8 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • CSA Standard C22.2 No. 182.1 • UL Classified to IEC60309-1 • UL Listed, File E146032
Nema Rating	Non-NEMA

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL430P9WR](#)



A Hubbell brand