

# Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male, Plug, 32A 380/415V, 3-Pole 4-Wire Grounding, Terminal Screws, Red, Watertight

By Hubbell Wiring Device-Kellems  
Catalog # [HBL432P3W](#)

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male, Plug, 32A 380/415V, 3-Pole 4-Wire Grounding, Terminal Screws, Red, Watertight



## Application

- High Ampacity Connections

## Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 3,000V AC Min
- Electrical - Max. Working Voltage - 600V AC RMS
- Environmental - Flammability - HB or Better per UL 94 or CSA C22.2 No. 0.17
- Environmental - Ingress Protection - IP67 Suitability
- Environmental - Moisture Resistance - Watertight per IEC 60309-1
- Environmental - Operating Temperature - Maximum Continuous 75°C
- Minimum - 40°C w/o impact
- Mechanical - Impact Resistance - Per CSA C22.2 No. 182.1 / UL1682
- Mechanical - Product Identification - Identification and ratings are a permanent part of the device housing.
- Mechanical - Terminal Identification - Terminals identified in accordance with North American and IEC conventions

## General

Catalog Number	HBL432P3W
Color	Red
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Item Type	Male Plug
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
Series	HBL Heavy Duty
Specifications	<ul style="list-style-type: none"><li>• Contact Carrier - High-Impact Thermoset</li><li>• Housing - Zytel® ST801 Nylon</li></ul>

Style  
Type  
UPC

• Locking Ring - Reinforced Thermoplastic Polyester  
• Retainer - High-Impact Thermoset  
• Terminal Screws - Stainless Steel  
Standard Service  
Watertight Plug  
783585404691

## Dimensions

Display Size Standard Sized

## Electrical Ratings

Amperage Rating 32 A  
Connectivity Pressure Terminal Screws  
Current / Amperage Rating 32 A  
Current Rating 32 A  
Phase Single Phase  
Voltage Rating 380 V 50Hz/440 V 60Hz V  
Voltage Rating Description 380 V 50Hz/440 V 60Hz

## Conductor Related

Cord Type All Portable  
Number Of Wires 4-Wire  
Wire Size #12 AWG to #8 AWG

## Certifications And Compliance

Industry Standard(s)

- CSA Standard C22.2 No. 182.1
- UL Classified to IEC60309-1
- UL Listed, File E146032

Nema Rating Non-NEMA

## Logistics

Carton Quantity 10



A Hubbell brand