



Wiring Device-Kellems

# Straight Blade Devices, Female Connector Body, Valise Series, Industrial/Commercial Grade, Straight, 2-Pole 3- Wire Grounding, 15A 125V, 5-15R



By Hubbell Wiring Device-Kellems  
Catalog # [HBL5969VBLK](#)

Straight Blade Devices, Female Connector Body, Valise Series, Industrial/Commercial Grade, Straight, 2-Pole 3- Wire Grounding, 15A 125V, 5-15R, Black, Single Pack.

### Features

- Hinged one piece body design for easy assembly
- Powerful, offsetting cord grips clamp on individual conductors
- Assembly screws are captive and will not fall out while wiring

### Application

Industrial/Commercial

### General

Cord Range	0.220"-.660" (5.6-16.8)
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	0.50
Insulation	Insulated Body
Item Type	Valise
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact

### Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 HB or better
- Environmental - IP Suitability - IP20
- Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #18-12 AWG. Standed copper wire

### Dimensions

Dimensions	2.68 in x 1.32 in x 2.68 in
Display Size	Standard
Height	2.68 in
Length	2.68 in
Weight	0.15 lb
Width	1.32 in

### Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

### Conductor Related

Conductor Range	#14 AWG to #12 AWG
Number Of Wires	3-Wire
Wire Size	#18 AWG to #12 AWG

### Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• CSA Certified to C22.2 No. 42 File 280C</li> <li>• NEMA® WD-6 Compliant</li> <li>• UL Listed to UL498 File E1706</li> </ul>
----------------------	--

Nema Rating	5-15R
Standards - RoHS Compliance Status	CM

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

[Catalogs - WDK Catalog Full 2023](#)  
[Warranty - Industrial & Commercial Products](#)

only

- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

Series	Valise®
Style	Standard
Temperature Rating	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Type	<ul style="list-style-type: none"><li>• Connector Body</li><li>• Connector Body</li></ul>
UPC	783585013275



**A proud member of the Hubbell Family.**

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_MX-HBL5969VBLK-SPEC-EN | REV 1/2024