

Locking Devices, Twist-Lock®, Industrial, Duplex Receptacle, 15A 250V, 2-Pole 3-Wire Grounding, L6-15R, Screw Terminal, Black

By Hubbell Wiring Device-Kellems
Catalog # [HBL4550](#)



Locking Devices, Twist-Lock®, Industrial, Duplex Flush Receptacle, 15A 250V, 2-Pole 3-Wire Grounding, NEMA L6-15R, Screw Terminal, Brown.

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.17
- Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #18 AWG - #10 AWG solid or stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

General

| | |
|------------------------------|---|
| Catalog Number | HBL4550 |
| EU RoHS Indicator | Yes |
| Environmental Conditions | Indoor Dry Unless Protected By Additional Means |
| Horsepower - Maximum | 1.5 |
| Item Type | 15A Duplex Flush Receptacle |
| Material | Thermoplastic |
| Material - Mounting Hardware | Screw Mounting |
| Number Of Poles | 2-Pole |
| Operating Temperature | Maximum continuous 75°C and minimum -40°C without Impact |
| Specifications | <ul style="list-style-type: none">• Base - RTP• Clamp - Brass• Contacts - Brass• Face - RTP• Ground Contact - Brass• Terminal Screws - Brass |
| Type | Receptacle |
| UPC | 783585002378 |

Dimensions

| | |
|--------------|-----------------------------|
| Dimensions | 3.29 in x 1.70 in x 1.17 in |
| Display Size | Standard Sized Product |

| | |
|--------|---------|
| Height | 1.17 in |
| Length | 3.29 in |
| Weight | 0.3 lb |
| Width | 1.7 in |

Electrical Ratings

| | |
|----------------------------|---------------------------|
| Amperage Rating | 15 A |
| Connectivity | Screw Terminals |
| Current / Amperage Rating | 15 A |
| Current Rating | 15 A |
| Dielectric Strength | Withstands 2,000V minimum |
| Phase | Single Phase |
| Voltage Rating | 250 V |
| Voltage Rating Description | 250 V |

Conductor Related

| | |
|-----------------|--------------------|
| Number Of Wires | 3-Wire |
| Wire Size | #18 AWG to #10 AWG |

Certifications And Compliance

| | |
|------------------------------------|--|
| Industry Standard(s) | <ul style="list-style-type: none">• Certified to CSA C22.2 No.42• Fed. Spec. W-C-596• Listed to UL 498 |
| Standards - RoHS Compliance Status | CM |

Logistics

| | |
|-----------------|------|
| Carton Quantity | 10 |
| Pallet Quantity | 5500 |

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Literature - EdgeConnect™ Technology FAQ](#)
[Specifications - HBL4550](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL4550-SPEC-EN | REV 10/2024