



Wiring Device-Kellems

Surge Protective Devices, SPIKESHIELD Wired-In Branch Panel Protection, TVSS Block, 100KA, 3PH 240/120V with Filter

By Hubbell Wiring Device-Kellems
Catalog # [HBL6W100C](#)



Surge Protective Devices, SPIKESHIELD Wired-In Branch Panel Protection, TVSS Block, 100KA, 3PH 240/120V with Filter

Application

Surface Mount Brick with Leads

General

EU RoHS Indicator	No
Environmental Conditions	Indoor and Outdoor
Indicator(s) Type	Green Status LED, Audible Alarm
Item Type	Wired-In Branch Panel Protection
Material	Steel
Material - Mounting Hardware	Mounting Screws
Operating Temperature	-40 Degrees F to 149 Degrees F (-40 C to 65 C)
Performance	<ul style="list-style-type: none"> Electrical - Diagnostics - Green Status LED's, Audible Alarm, Dry Contacts Electrical - Surge Current per Phase - 100kA Environmental - Operating Temperature - -40°F to 140°F (-40°C to 60°C) Mechanical - Terminal Accommodation - #10 AWG 18.0" Wire Leads
Response Time	5
Series	Wired-In Panels
Type	100kA
UPC	783585120812

Dimensions

Display Size 100kA Peak

Electrical Ratings

Connectivity	Leads
Frequency Rating	60 Hz
Phase	Three Phase
Voltage Rating	<ul style="list-style-type: none"> Delta split phase 240 VAC Delta split phase 120 VAC
Voltage Rating Description	240/120 VAC Delta Split Phase

Certifications and Compliance

Industry Standard(s) cULus UL1449-3Rd Edition Type 2 Spd

Product Assets

[Catalogs - WDK Catalog Full 2023](#)
[Warranty - SPD Series: 320kA, 160kA, 100kA, 120kA, 80MkA & 50kA](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_MX-HBL6W100C-SPEC-EN | REV 1/2024