

Locking Devices, Midget Twist-Lock®, Industrial, Female Straight Connector, 15A 125/250V AC, 3-Pole 3-Wire Non Grounding, NEMA ML-3R, Screw Terminal.



By Hubbell Wiring Device-Kellems
Catalog # [HBL7484](#)

Locking Devices, Midget Twist-Lock®, Industrial, Female Straight Connector, 15A 125/250V AC, 3-Pole 3-Wire Non Grounding, NEMA ML-3R, Screw Terminal, Black.

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.17
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact)
- Mechanical - Terminal Accomodation - #18 AWG - #14 AWG stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

General

Catalog Number	HBL7484
Color	Black
Cord Range	0.281"-0.421"(7.1-10.7)
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	15A Midget Twist-Lock® Connector
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none"> • Contact Holder - Phenolic • Contacts - Brass • Housing - Nylon • Terminal Clamp - Zinc plated steel with black lacquer finish • Terminal Screws - #5-40 Brass

Temperature Rating

Maximum Continuous: 75° C;
Minimum Continuous: -40° C
w/o impact, -25° with impact.
Connector Body
783585237381

Type
UPC

Dimensions

Dimensions	1.17 in x 1.17 in x 2.42 in
Display Size	Midget Locking
Height	2.42 in
Length	1.17 in
Weight	0.05 lb
Width	1.17 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	125/250 V
Voltage Rating Description	125/250 V

Conductor Related

Cable Range	0.281 - 0.421 in
Conductor Range	#14 AWG to #12 AWG
Number Of Wires	3-Wire
Wire Size	#18 AWG to #14 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA C22.2 No.42 • Listed to UL 498
Nema Rating	ML-3R

Logistics

Carton Quantity	10
-----------------	----

Pallet Quantity

6600

[Catalogs - WDK Catalog Full 2024](#)

[Specifications - HBL7484](#)

[Warranty - Industrial & Commercial Products](#)

Product Assets



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
WDK_MX-HBL7484-SPEC-EN | REV 1/2025