

Locking Devices, Twist-Lock®, Industrial, Female Connector Body, 15A 250V, 2-Pole 3-Wire Grounding, L6-15R, Screw Terminal, Black and White

By Hubbell Wiring Device-Kellems
Catalog # [HBL4579C](#)

Locking Devices, Twist-Lock®, Industrial, Female Insulgrip® Connector Body, 15A 250V, 2-Pole 3-Wire Grounding, NEMA L6-15R, Screw Terminal, Black and White Nylon.



Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - HB or better per UL94 or CSA 22.2 No. 0.6
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #18 - #10 AWG stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

General

Catalog Number	HBL4579C
Color	Noir, blanc
Cord Range	0.230"-0.720"(5.8-18.3)
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	15A Grounding Insulgrip® Connector
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none"> • Assembly Screws - Steel - nickel plated • Contacts - Brass • Housing / Cord Clamp - Nylon • Terminal Clamp - Cold rolled steel - nickel plated • Terminal Retainer - Clear polycarbonate

Temperature Rating

Type
UPC

Dimensions

Dimensions	1.53 in x 1.53 in x 2.78 in
Display Size	Standard
Height	2.78 in
Length	1.53 in
Weight	0.15 lb
Width	1.53 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	250 V
Voltage Rating Description	250 V

Conductor Related

Cable Range	0.230 - 0.720 in
Number Of Wires	3-Wire
Wire Size	#18 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA C22.2 No.42 • Fed.Spec. W-C-596 • Listed to UL 498
Nema Rating	L6-15R

- Terminal Screws - #8-32 Brass (Phillips / Slotted / Robertson)
- Maximum Continuous: 75° C;
Minimum Continuous: -40° C w/o impact, -25° with impact.
Connector Body
783585170107

Standards - RoHS Compliance CM
Status

Logistics

Carton Quantity 10
Pallet Quantity 3600

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL4579C](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL4579C-SPEC-EN | REV 10/2024