

Straight Blade Devices, Female Connector Body, Heavy Duty, Industrial/Commercial Grade, Straight, 3-Pole 3-Wire Non Grounding, 50A 125/250V, 10-50R



By Hubbell Wiring Device-Kellems
Catalog # [HBL7515C](#)

Straight Blade Devices, Female Connector Body, Heavy Duty, Industrial/Commercial Grade, Straight, 3-Pole 3-Wire Non Grounding, 50A 125/250V, 10-50R, Black, Single Pack.

Application

Industrial/Commercial

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 HB
- Environmental - IP Suitability - IP20
- Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #12 AWG through #4 AWG copper wire only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	HBL7515C
Color	Black
Cord Range	0.625"-1.218"
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	3
Insulation	Insulated Body
Item Type	Insulgrip
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Extra Heavy Duty
Specifications	<ul style="list-style-type: none">• Blade Holder - Reinforced Thermoplastic Polyester• Blades - Brass

Style
Temperature Rating

Type
UPC

Dimensions

Dimensions	5.75 in x 2.88 in x 2.88 in
Display Size	Standard
Height	2.88 in
Length	5.75 in
Weight	1 lb
Width	2.88 in

Electrical Ratings

Amperage Rating	50 A
Connectivity	Screw Terminals
Current / Amperage Rating	50 A
Current Rating	50 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	125/250 V
Voltage Rating Description	125/250 V

Conductor Related

Conductor Range	#10 AWG
Number Of Wires	3-Wire
Number of Conductors	3-Wire Non-Grounding
Wire Size	#12 AWG to #4 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• CSA Certified• UL Listed File E1706
----------------------	------------------------------------------------------------------------------------------------

- Box Terminals - Copper Alloy
 - Cord Clamps - Reinforced Thermoplastic Polyester
 - Housing - Supertough Nylon Non-Grounding
- Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
- Connector Body
783585015118

Nema Rating 10-50R

Product Assets

Logistics

Carton Quantity 10
Pallet Quantity 910

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL7515C](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL7515C-SPEC-EN | REV 10/2024