

HUBBELL
Wiring Device-Kellems

**Locking Devices, Twist-Lock®,
Industrial, Duplex Receptacle, 10A
250/15A 125V, 2-Pole 3-Wire
Grounding, Non-NEMA, Screw
Terminal, Black**

By Hubbell Wiring Device-Kellems
Catalog # [HBL7580](#)

Twist-Lock® Industrial Duplex Flush Receptacle, 10A 250/15A
125V, 3-Pole 3-Wire Non-Grounding, Non-NEMA, Screw Terminal
RTP



Performance

- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - V2 or better per UL94/CSA 22.2 No.0.17
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #18 AWG -#10 AWG solid or stranded copper wire only.
- Mechanical - Terminal Accommodation - #18-#10 AWG solid or stranded copper wire.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

General

Catalog Number	HBL7580
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	10A/15A Non-Grounding Duplex Flush Receptacle
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none">• Base - RTP• Clamp - Brass• Contacts - Brass• Face - RTP• Ground Contact - Brass• Terminal Screws - Brass
Type	Receptacle
UPC	783585002354

Dimensions

Dimensions	3.29 in x 1.7 in x 1.17 in
------------	----------------------------

Display Size	Standard Sized Product
Height	1.17 in
Length	3.29 in
Weight	0.3 lb
Width	1.7 in

Electrical Ratings

Amperage Rating	10/15 A
Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	10/15 A
Current Rating	10 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	250/125 V
Voltage Rating Description	250/125 V

Conductor Related

Number Of Wires	3-Wire
Wire Size	#18 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Certified to CSA C22.2 No.42• Fed. Spec. W-C-596• Listed to UL 498
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
Pallet Quantity	5500

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Specifications - HBL7580](#)
- [Warranty - Industrial & Commercial Products](#)

