

## Locking Devices, Twist-Lock®, Industrial, Flanged Inlet, 15A 125V, 2-Pole 3-Wire Grounding, L5-15P, Screw Terminal, White

By Hubbell Wiring Device-Kellems  
Catalog # [HBL4716C](#)

Locking Devices, Twist-Lock®, Industrial, Insulgrip® Flanged Inlet, 15A 125V, 2-Pole 3-Wire Grounding, NEMA L5-15P, Screw Terminal, Nylon casing, Back wired, White.

### Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.17
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #18 AWG - #10 AWG solid or stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

### General

Catalog Number	HBL4716C
Color	White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	15A Grounding Insulgrip® Flanged Inlet
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none"> <li>• Assembly Screws - Steel - zinc plated</li> <li>• Blades - Brass</li> <li>• Housing - Nylon</li> <li>• Mounting Screw - Nickel plated brass</li> <li>• Terminal Clamp - #8-32 Brass (Phillips / Slotted / Robertson)</li> <li>• Terminal Clamp - Cold rolled steel - nickel plated</li> </ul>



Temperature Rating	Terminal Retainer - Clear polycarbonate Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Flanged Inlet
UPC	783585171050

### Dimensions

Dimensions	2.56 in x 2.56 in x 1.72 in
Display Size	Standard Sized Product
Height	1.72 in
Length	2.56 in
Weight	0.15 lb
Width	2.56 in

### Electrical Ratings

Amperage Rating	15 A
Connectivity	Back Wired Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

### Conductor Related

Number Of Wires	3-Wire
Wire Size	#18 AWG to #10 AWG

### Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• Certified to CSA C22.2 No.42</li> <li>• Fed.Spec.W-C-596</li> <li>• Listed to UL 498</li> </ul>
Nema Rating	L5-15P
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity 10  
Pallet Quantity 4500

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - HBL4716C](#)  
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK\_MX-HBL4716C-SPEC-EN | REV 10/2024