



Locking Devices, Twist-Lock®, Industrial, Single Flush Receptacle, 10A 250V, 15A 125V, 3-Pole 3-Wire Non-Grounding, Non-NEMA, Screw Terminal Phenolic.

By Hubbell Wiring Device-Kellems
Catalog # [HBL7582](#)



Locking Devices, Twist-Lock®, Industrial, Single Flush Receptacle, 10A 250V, 15A 125V, 3-Pole 3-Wire Non-Grounding, Non-NEMA, Screw Terminal, Black Phenolic.

Features

- Thermoset construction offers high heat resistance
- High performance copper alloy contacts
- Corrosion resistant zinc plated steel one-piece mounting strap

Application

Heavy Duty Industrial

General

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	10A/15A Single Receptacle
Material	Phenolic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 2,000V minimum • Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.17 • Environmental - Moisture Resistance - IP20 Suitability • Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact) • Mechanical - Terminal Accommodation - #18 AWG -#10 AWG solid or stranded copper wire only. • Mechanical - Terminal Identification - Terminals

Dimensions

Dimensions	3.28 in x 1.5 in x 1.19 in
Display Size	Standard Sized Product
Height	1.19 in
Length	3.28 in
Weight	0.15 lb
Width	1.5 in

Electrical Ratings

Amperage Rating	10/15 A
Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	10/15 A
Current Rating	10 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	250/125 V
Voltage Rating Description	250/125 V

Conductor Related

Number Of Wires	3-Wire
Wire Size	#18 AWG to #10 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA C22.2 No.42 • Fed. Spec. W-C-596 • Listed to UL 498
----------------------	--

Standards - RoHS Compliance Status	CM
------------------------------------	----

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2023](#)
[Warranty - Industrial & Commercial Products](#)

identified in accordance
with UL 498

Type

- Receptacle
- Receptacle

UPC

783585237718



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_MX-HBL7582-SPEC-EN | REV 1/2024