

# Locking Devices, Twist-Lock®, Industrial, Male Plug, 15A 125V, 2-Pole 3-Wire Grounding, L5-15P, Screw Terminal, Black and White, Angled,

By Hubbell Wiring Device-Kellems  
Catalog # [HBL4720CA](#)



Locking Devices, Twist-Lock®, Industrial, Male Insulgrip® Plug, 15A 125V, 2-Pole 3-Wire Grounding, NEMA L5-15P, Screw Terminal, Black and White Nylon, 8 position angle.

## Application

Extra Heavy Duty Industrial

## Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - HB or better per UL94 or CSA 22.2 No. 0.6
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #16 AWG - #8 AWG stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

## General

Catalog Number	HBL4720CA
Color	Black, White
Cord Range	0.325"-0.655"(8.3-16.6)
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	0.5
Item Type	15A Grounding Insulgrip® Plug
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none"><li>• Assembly Screws - Steel - nickel plated</li><li>• Blades - Brass</li><li>• Housing / Cord Clamp - Nylon</li><li>• Terminal Clamp - Cold rolled steel - nickel plated</li></ul>

- Terminal Retainer - Clear polycarbonate
- Terminal Screws - #8-32 Brass (Phillips / Slotted / Robertson)

Type  
UPC

Plugs  
783585171203

## Dimensions

Dimensions	2.08 in x 1.52 in x 1.21 in
Display Size	Standard Sized
Height	1.21 in
Length	2.08 in
Weight	0.15 lb
Width	1.52 in

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

## Conductor Related

Cable Range	0.325 - 0.655 in
Cord Type	All Listed Portables
Number Of Wires	3-Wire
Wire Size	#16 AWG to #8 AWG

## Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• Certified to CSA C22.2 No.42</li><li>• Fed.Spec. W-C-596</li><li>• Listed to UL 498</li></ul>
----------------------	---

Nema Rating L5-15P  
Standards - RoHS Compliance CM  
Status

Pallet Quantity 4500

**Product Assets**

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - HBL4720CA](#)  
[Warranty - Industrial & Commercial Products](#)

**Logistics**

Carton Quantity 10



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK\_MX-HBL4720CA-SPEC-EN | REV 10/2024