

## Locking Devices, Midget Twist-Lock®, Industrial, Flanged Inlet, 15A 125V AC, NEMA ML-2P, Screw Terminal, Stainless Steel Flange.

By Hubbell Wiring Device-Kellems  
Catalog # [HBL7595](#)



Locking Devices, Midget Twist-Lock®, Industrial, Flanged Inlet, 15A 125V AC, 2-Pole 3-Wire Grounding, NEMA ML-2P, Screw Terminal, Stainless Steel Flange.

### Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.17
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #18 AWG - #14 AWG solid or stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

### General

Catalog Number	HBL7595
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	15A Midget Twist-Lock® Flanged Inlet
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none"><li>• Base - Phenolic</li><li>• Blades - Brass</li><li>• Flange - Stainless Steel</li><li>• Terminal Screws - #5-40 Brass</li></ul>
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Flanged Inlet
UPC	783585237794

### Dimensions

Dimensions	2.06 in x 1.63 in x 1.00 in
Display Size	Midget Locking
Height	1 in
Length	2.06 in
Weight	0.1 lb
Width	1.63 in

### Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

### Conductor Related

Number Of Wires	3-Wire
Wire Size	#18 AWG to #14 AWG

### Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• Certified to CSA C22.2 No.42</li><li>• Listed to UL 498</li></ul>
Nema Rating	ML-2P

### Logistics

Carton Quantity	10
Pallet Quantity	4500

### Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - HBL7595](#)  
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand