

# Locking Devices, Twist-Lock®, Industrial, Male Plug, 15A 125V, 2-Pole 3-Wire Grounding, L5-15P, Screw Terminal, Black

By Hubbell Wiring Device-Kellems  
Catalog # [HBL4720CBK](#)



Locking Devices, Twist-Lock®, Insulgrip® Plug, 15A, 125V, 2 Pole, 3 Wire Grounding, NEMA L5-15P, All black nylon

## Application

Extra Heavy Duty Industrial

## Performance

- Electrical-Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Mechanical - Terminal Accommodation - #18 - #10 AWG stranded copper wire only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498
- Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.6
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C
- Minimum -40°C (w/o impact)

## General

|                              |   |
|------------------------------|---|
| Catalog Number               | HBL4720CBK  |
| Color                        | Black   |
| Cord Range                   | 0.230"-0.720"(5.8-18.3)   |
| EU RoHS Indicator            | Contact Manufacturer  |
| Environmental Conditions     | Indoor Dry Unless Protected By Additional Means   |
| Horsepower - Maximum         | 0.5   |
| Item Type                    | 15A Insulgrip® Plug   |
| Listings                     | <ul style="list-style-type: none"><li>• UL 498</li><li>• Fed.Spec. W-C-596</li><li>• CSA C22.2 No.42</li></ul>  |
| Material                     | Nylon   |
| Material - Mounting Hardware | Cord Mounted  |
| Number Of Poles              | 2-Pole  |
| Operating Temperature        | Maximum continuous 75°C and minimum -40°C without Impact  |
| Specifications               | <ul style="list-style-type: none"><li>• Assembly Screws - Steel - nickel plated</li><li>• Blades - Brass</li><li>• Housing / Cord Clamp - Nylon</li></ul> |

UPC

- Terminal Clamp - Cold rolled steel - nickel plated
  - Terminal Retainer - Clear polycarbonate
  - Terminal Screws - #8-32 Brass (Phillips / Slotted / Robertson)
- 783585172163

## Dimensions

|              |                             |
|--------------|-----------------------------|
| Dimensions   | 1.53 in x 1.53 in x 1.97 in |
| Display Size | Standard Sized              |
| Height       | 1.97 in                     |
| Length       | 1.53 in                     |
| Weight       | 0.15 lb                     |
| Width        | 1.53 in                     |

## Electrical Ratings

|                            |                           |
|----------------------------|---------------------------|
| Amperage Rating            | 15 A                      |
| Connectivity               | Pressure Terminal Screws  |
| Current / Amperage Rating  | 15 A                      |
| Current Rating             | 15 A                      |
| Dielectric Strength        | Withstands 2,000V minimum |
| Phase                      | Single Phase              |
| Voltage Rating             | 125 VAC                   |
| Voltage Rating Description | 125 VAC                   |

## Conductor Related

|                 |                      |
|-----------------|----------------------|
| Cord Type       | All Listed Portables |
| Number Of Wires | 3-Wire Grounding     |
| Wire Size       | #18 AWG to #10 AWG   |

## Certifications And Compliance

|                                    |   |
|------------------------------------|---|
| Industry Standard(s)               | <ul style="list-style-type: none"><li>• Certified to CSA C22.2 No.42</li><li>• Fed.Spec. W-C-596</li><li>• Listed to UL 498</li></ul> |
| Nema Rating                        | L5-15P  |
| Standards - RoHS Compliance Status | CM  |

## Logistics

Carton Quantity 10

Catalogs - WDK Catalog Full 2024  
Specifications - HBL4720CBK  
Warranty - Industrial & Commercial Products

## Product Assets

---



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK\_MX-HBL4720CBK-SPEC-EN | REV 10/2024