


HUBBELL
Wiring Device-Kellems

**Locking Devices, Twist-Lock®,
Industrial, Flanged Inlet, 50A
250V/600V AC, Non-NEMA, Screw
Terminal, Zinc plated steel casing,
thermoset interior**

By Hubbell Wiring Device-Kellems
Catalog # [HBL7958](#)

Locking Devices, Twist-Lock®, Industrial, Flanged Inlet, 50A
250V/600V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw
Terminal, Zinc plated steel casing, thermoset interior, Metallic



General

Application	Extra Heavy Duty Industrial
Catalog Number	HBL7958
Color	Metallic
	Métallique
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	50A Flanged Inlet
Material	Steel, Zinc Plated
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	Electrical - Current Interrupting - Certified for current interrupting at full rated current
	Electrical - Dielectric Voltage - Withstands 2,000V minimum
	Environmental - Flammability - UL 94 V0
	Environmental - Operating Temperatures - Maximum continuous 75°C minimum - 40°C (w/o impact)
	Mechanical - Terminal Accommodation - #10 AWG - #6 AWG solid or stranded copper wire only
Type	Flanged Inlet
UPC	783585237589

Dimensions

Dimensions	2.14 in x 3.50 in x 2.62 in
Display Size	Standard Sized Product
Height	2.62 in
Length	2.14 in
Weight	0.85 lb
Width	3.5 in

Electrical Ratings

Amperage Rating	50 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	50 A
Current Rating	50 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Three Phase
Voltage Rating	250 VDC/600 VAC
Voltage Rating Description	250 VDC/600 VAC

Conductor Related

Number Of Wires	4-Wire
Wire Size	#8 AWG to #4 AWG

Certifications And Compliance

Industry Standard(s)	Certified to CSA C22.2 No.42 Listed to UL 498
----------------------	--

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL7958-SPEC-EN | REV 6/2024