

HUBBELL
Wiring Device-Kellems

**Straight Blade Devices,
Receptacles, Duplex, Tamper
Resistant Hospital Grade, 2-Pole 3-
Wire Grounding, 15A 125V, 5-15R,
Ivory, Single Pack**

By Hubbell Wiring Device-Kellems
Catalog # [HBL8200SGIA](#)

Straight Blade Devices, Receptacles, Duplex, Tamper Resistant
Hospital Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Ivory,
Single Pack.



General

Application	Extra Heavy Duty Hospital Grade
Catalog Number	HBL8200SGIA
Color	Ivory
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	0.5
Item Type	Traditional Duplex
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	Electrical - Current Interrupting - Certified for current interrupting at full rated current Electrical - Dielectric Voltage - Withstands 2,000V minimum Environmental - Flammability - UL 94V-0 and UL 94-5 VA Environmental - IP Suitability - IP20 Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact) Mechanical - Ground Terminal Accommodation - #12-#10 AWG stranded or solid copper wire only Mechanical - Product Identification - Ratings are a permanent part of the device Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA
Series	Hospital Grade
Style	Tamper Resistant
Type	Receptacle
UPC	783585152233

Dimensions

Dimensions	3.29 in x 1.65 in x 1.27 in
Display Size	Standard Sized Product
Height	1.27 in
Length	3.29 in
Weight	0.35 lb
Width	1.65 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Wire Leads
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#12 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	CSA Certified, C22.2, No. 42 File 285 Fed. Spec. W-C-596 NEMA® WD-6 Compliant UL Listed to UL498 File No. E2186
Nema Rating	5-15R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL8200SGIA-SPEC-EN | REV 6/2024