

Straight Blade Devices,
Receptacles, Duplex, Tamper
Resistant Hospital Grade, 2-Pole 3-
Wire Grounding, 15A 125V, 5-15R,
Ivory, Single Pack

By Hubbell Wiring Device-Kellems
Catalog # [HBL8200SGIA](#)



Straight Blade Devices, Receptacles, Duplex, Tamper Resistant
Hospital Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Ivory,
Single Pack.

Application

Extra Heavy Duty Hospital Grade

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94V-0 and UL 94-5 VA
- Environmental - IP Suitability - IP20
- Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Ground Terminal Accommodation - #12-#10 AWG stranded or solid copper wire only
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

| | |
|------------------------------|--|
| Catalog Number | HBL8200SGIA |
| Color | Ivory |
| EU RoHS Indicator | No |
| Environmental Conditions | Indoor Dry Unless Protected By Additional Means |
| Horsepower - Maximum | 0.5 |
| Item Type | Traditional Duplex |
| Material | Thermoplastic |
| Material - Mounting Hardware | Screw Mounting |
| Number Of Poles | 2-Pole |
| Operating Temperature | Maximum continuous 75°C and minimum -40°C without Impact |
| Series | Hospital Grade |
| Specifications | <ul style="list-style-type: none">• Automatic Self-Grounding Clip - Stainless steel• Base - PBT• Contacts - .037 in. (.9) Nickel plated brass• Face - PBT |

| | |
|-------|--|
| Style | Lead Wires - 6 in. (15.24), #12 AWG 65/30 stranded copper wire |
| Type | Mounting Screws - Zinc plated |
| UPC | Mounting Strap - .050 in. (1.3) Nickel plated brass |
| | Tamper Resistant Receptacle |
| | 783585152233 |

Dimensions

| | |
|--------------|-----------------------------|
| Dimensions | 3.29 in x 1.65 in x 1.27 in |
| Display Size | Standard Sized Product |
| Height | 1.27 in |
| Length | 3.29 in |
| Weight | 0.35 lb |
| Width | 1.65 in |

Electrical Ratings

| | |
|----------------------------|---------------------------|
| Amperage Rating | 15 A |
| Connectivity | Wire Leads |
| Current / Amperage Rating | 15 A |
| Current Rating | 15 A |
| Dielectric Strength | Withstands 2,000V minimum |
| Phase | Single Phase |
| Voltage Rating | 125 V |
| Voltage Rating Description | 125 V |
| Wattage | 1875 W |

Conductor Related

| | |
|-----------------|--------------------|
| Number Of Wires | 3-Wire |
| Wire Size | #12 AWG to #10 AWG |

Certifications And Compliance

| | |
|----------------------|---|
| Industry Standard(s) | <ul style="list-style-type: none">• CSA Certified, C22.2, No. 42 File 285 |
|----------------------|---|

| | |
|-------------|---|
| Nema Rating | <ul style="list-style-type: none">Fed. Spec. W-C-596NEMA® WD-6 CompliantUL Listed to UL498 File No. E2186 |
| | 5-15R |

Logistics

Carton Quantity 10

Product Assets

- Catalogs - WDK Catalog Full 2024
- Specifications - HBL8200SGIA
- Warranty - Industrial & Commercial Products

