

## Straight Blade Devices, Receptacles, Flanged, Commercial /Industrial Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, brown, Single Pack.

By Hubbell Wiring Device-Kellems  
Catalog # [HBL5256](#)

Straight Blade Devices, Receptacles, Flanged, Commercial  
/Industrial Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R,  
brown, Single Pack.



### Application

- Heavy Duty

### Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 V-0
- Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

### General

Catalog Number	HBL5256
Color	Brown
Cord Range	0.230"-0.720" (5.8-18.3)
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	0.5
Item Type	Flanged Single
Material	Stainless Steel
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none"><li>• Face - Phenolic</li><li>• Mounting Screw - Nickel plated brass</li><li>• Power Contacts - .040" (1.0) Brass</li><li>• Terminal Screw - #8-32 Brass, Multiple Drive</li></ul>

UPC 783585013046

### Dimensions

Display Size Standard Sized Product  
Weight 0.15 lb

### Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875 W

### Conductor Related

Number Of Wires 3-Wire  
Wire Size #14 AWG to #10 AWG

### Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• Certified to CSA, C22.2, No. 42</li><li>• NEMA® WD-6 Compliant</li><li>• UL Listed, File E2186</li></ul>
Nema Rating	5-15R
Standards - RoHS Compliance Status	CM

### Logistics

Carton Quantity 10  
Pallet Quantity 5000

### Product Assets

[Catalogs - WDK Catalog Full 2024](#)



A Hubbell brand