

Straight Blade Devices, Receptacles, Single, Hospital Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Brown, Single Pack

By Hubbell Wiring Device-Kellems
Catalog # [HBL8210](#)



Straight Blade Devices, Receptacles, Single, Hospital Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Brown, Single Pack.

Application

- Extra Heavy Duty Hospital Grade

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94V-0 and UL 94-5 VA
- Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

| | |
|------------------------------|--|
| Catalog Number | HBL8210 |
| Color | Brown |
| EU RoHS Indicator | Yes |
| Environmental Conditions | Indoor Dry Unless Protected By Additional Means |
| Horsepower - Maximum | 0.5 |
| Item Type | Single Receptacle |
| Material | Nylon |
| Material - Mounting Hardware | Screw Mounting |
| Number Of Poles | 2-Pole |
| Operating Temperature | Maximum continuous 75°C and minimum -40°C without Impact |
| Series | Hospital Grade |
| Specifications | <ul style="list-style-type: none">• Automatic Self-grounding Clip - Stainless steel• Base - PBT• Clamp - Nickel plated brass• Face - Nylon• Ground Contact - Nickel plated brass• Mounting Screws - Stainless steel |

| | |
|-------|--------------------|
| Style | Finder Groove Face |
| Type | Single Receptacle |
| UPC | 783585016214 |

Dimensions

| | |
|--------------|-----------------------------|
| Dimensions | 3.28 in x 1.63 in x 1.19 in |
| Display Size | Standard Sized Product |
| Height | 1.19 in |
| Length | 3.28 in |
| Weight | 0.2 lb |
| Width | 1.63 in |

Electrical Ratings

| | |
|----------------------------|-------------------------------------|
| Amperage Rating | 15 A |
| Connectivity | Back and Side Wired Screw Terminals |
| Current / Amperage Rating | 15 A |
| Current Rating | 15 A |
| Dielectric Strength | Withstands 2,000V minimum |
| Phase | Single Phase |
| Voltage Rating | 125 V |
| Voltage Rating Description | 125 V |
| Wattage | 1875 W |

Conductor Related

| | |
|-----------------|--------------------|
| Number Of Wires | 3-Wire |
| Wire Size | #14 AWG to #10 AWG |

Certifications And Compliance

| | |
|----------------------|--|
| Industry Standard(s) | <ul style="list-style-type: none">• Certified to CSA, C22.2, No. 42 File 285• Fed. Spec. W-C-596• NEMA® WD-6 Compliant• UL Listed to UL498 File No. E2186 |
| Nema Rating | 5-15R |

- Mounting Strap - .050 in. (1.3) Brass
- Power Contacts - .037 in. (.9) Brass

Standards - RoHS Compliance CM
Status

Logistics

Carton Quantity 10

Product Assets

[Catalogs - WDK Catalog Full 2024](#)

[Literature - EdgeConnect™ Technology FAQ](#)

[Specifications - HBL8210](#)

[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL8210-SPEC-EN | REV 10/2024