

HUBBELL
Wiring Device-Kellems

**Straight Blade Devices,
Receptacles, RTP, Industrial Grade,
2-Pole 3-Wire Grounding, 50A
250V, 6-50R, Black, Single Pack.**

By Hubbell Wiring Device-Kellems
Catalog # [HBL9367](#)

Designed for plug-in EV charging applications, Hubbell's 6-50R receptacle is a premium and dependable solution to exceed the requirements of electric vehicle owners. This receptacle ensures a safe and efficient charging experience, providing peace of mind to EV users.



Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 V-0
- Environmental - IP Suitability - IP20
- Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #12 AWG through #4 AWG copper wire only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	HBL9367
Color	Noir
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	3
Item Type	Single
Material	Thermoplastic/Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none">• Brass - Box Terminals• Brass - Ground Shunt• Housing - Reinforced Thermoplastic Polyester• Mounting Plate - .062 in. (1.5) Pre-Plated Steel
Type	Receptacle
UPC	783585015279

Dimensions

Dimensions	3.28 in x 2.25 in x 2.23 in
Display Size	Standard Sized Product
Height	2.23 in
Length	3.28 in
Weight	0.45 lb
Width	2.25 in

Electrical Ratings

Amperage Rating	50 A
Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	50 A
Current Rating	50 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	250 V
Voltage Rating Description	250 V
Wattage	12500 W

Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#12 AWG to #4 AWG

Certifications And Compliance

Industry Standard(s)	UL, CSA, Fed Spec
Nema Rating	6-50R

Logistics

Carton Quantity	10
Pallet Quantity	2560

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Electric Vehicle Charger Receptacle Specifications - HBL9367](#)
- [Warranty - Industrial & Commercial Products](#)



A Hubbell brand