

Straight Blade Devices, Male Inlets, Flanged, Industrial/Commercial, 15A 125V, 2-Pole 3-Wire Grounding, 5- 15P, White, Single Pack

By Hubbell Wiring Device-Kellems
Catalog # [HBL5278C](#)

Straight Blade Devices, Male Inlets, Flanged, Industrial/Commercial, 15A 125V, 2-Pole 3-Wire Grounding, 5-15P, White, Single Pack.

Application

- Extra Heavy Duty Industrial

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 V-2
- Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #18-#10 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	HBL5278C
Color	Blanc
Cord Range	0.230"-0.360" (5.8-18.3)
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	0.5
Insulation	Insulated Body
Item Type	Standard Single
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Insulgrip®
Specifications	<ul style="list-style-type: none"> • Assembly Screws - Steel - nickel plated • Blades - Brass • Housing - Nylon • Mounting Screws - Nickel plated brass



Style
Temperature Rating

Type
UPC

Dimensions

Dimensions	1.71 in x 1.69 in x 1.71 in
Display Size	Standard Sized Product
Height	1.71 in
Length	1.71 in
Weight	0.1 lb
Width	1.69 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V
Wattage	1875 W

Conductor Related

Conductor Range	#18 AWG to #10 AWG
Number Of Wires	3-Wire
Wire Size	#18 AWG to #12 AWG

Certifications And Compliance

- Terminal Clamp - Cold rolled steel - nickel plated
- Terminal Retainer - Clear polycarbonate
- Terminal Screws - #8-32 Brass, Multiple Drive

Standard
Maximum Continuous: 75° C;
Minimum Continuous: -40° C w/o impact, -25° with impact.
Flanged Inlet
783585173504

Industry Standard(s) • Certified to CSA, C22.2, No. 42
• NEMA® WD-6 Compliant
• UL Listed, File E2186

Nema Rating 5-15P
Standards - RoHS Compliance CM
Status

Carton Quantity 10
Pallet Quantity 4500

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL5278C](#)
[Warranty - Industrial & Commercial Products](#)

Logistics



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL5278C-SPEC-EN | REV 10/2024