

Straight Blade Devices, Male Plug, Insulgrip Heavy Duty, Industrial/Commercial Grade, Straight, 2-Pole 3- Wire Grounding, 15A 125V, 5-15P and White

By Hubbell Wiring Device-Kellems
Catalog # [HBL5280C](#)



Straight Blade Devices, Male Plug, Insulgrip Heavy Duty, Industrial/Commercial Grade, Straight, 2-Pole 3- Wire Grounding, 15A 125V, 5-15P, Black and White, Single Pack, With.

Application

Industrial/Commercial Grade

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 HB or better
- Environmental - IP Suitability - IP20
- Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #18-10 AWG. Standed copper wire only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	HBL5280C
Color	Black, White
EU RoHS Indicator	Contact Manufacturer
Horsepower - Maximum	0.5
Item Type	Insulgrip Plug
Material	Polycarbonate
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Insulgrip®
Specifications	<ul style="list-style-type: none"> • Assembly Screws - Nickel plated steel • Blade Holder - Nylon • Blades - .060 in. (1.5) Brass • Housing/Cord Clamp - Nylon • Terminal Clamp - Nickel plated steel • Terminal Retainer - Clear Polycarbonate

Style	Standard
Type	Plug
UPC	783585173658
	• Terminal Screws - #8-32 Brass , multiple drive

Dimensions

Dimensions	1.52 in x 1.52 in x 1.96 in
Height	1.96 in
Length	1.52 in
Weight	0.15 lb
Width	1.52 in

Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V

Conductor Related

Conductor Range	#18 AWG to #10 AWG
Number Of Wires	3-Wire
Wire Size	#18 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • NEMA® WD-6 Compliant • UL Listed to UL498 File E1706
Nema Rating	5-15P

Logistics

Carton Quantity	10
Pallet Quantity	4500



A Hubbell brand