

Straight Blade Devices, Male Plug, Nylon, 4-Position, Heavy Duty, Industrial/Commercial Grade, Angled, 3-Pole 4-Wire Grounding, 30A 125/250V, 14-30P.

By Hubbell Wiring Device-Kellems
Catalog # [HBL9432C](#)



Engineered specifically for EV charging applications, Hubbell's 14-50P straight blade angled plug stands out as a superior and reliable choice, fully compatible with established EV charging standards. This sturdy plug is crafted to offer exceptional durability, safety, and high performance, making it the ideal choice for environments that demand reliability in EV power delivery.

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 HB
- Environmental - IP Suitability - IP20
- Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #12 AWG through #4 AWG copper wire only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	HBL9432C
Color	Black
Cord Range	0.625"-1.310"
EU RoHS Indicator	Contact Manufacturer
Horsepower - Maximum	2
Material	Nylon
Number Of Poles	3-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Extra Heavy Duty
Specifications	<ul style="list-style-type: none">• Blade Holder - Reinforced Thermoplastic Polyester• Blades - Brass• Box Terminals - Copper Alloy• Cord Clamps - Reinforced Thermoplastic Polyester• Housing - Supertough Nylon

Style	Grounding
Type	Plug
UPC	783585015446

Dimensions

Dimensions	4.5 in x 3.38 in x 2.37 in
Height	2.37 in
Length	4.5 in
Weight	0.8 lb
Width	3.38 in

Electrical Ratings

Amperage Rating	30 A
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	<ul style="list-style-type: none">• 125 V• 250 V
Voltage Rating Description	125/250 V
Wattage	7500 W

Conductor Related

Number Of Wires	4-Wire
Wire Size	#12 AWG to #4 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Certified to CSA• UL Listed File E1706
Nema Rating	14-30P

Logistics

Carton Quantity	5
Pallet Quantity	765



A Hubbell brand