

Switches and Lighting Controls, Industrial Grade, Disconnect Switches, Replacement Switch, Three Pole, 60A 600V AC, Screw Terminals, Gray

By Hubbell Wiring Device-Kellems
Catalog # [HBLDS60100RS](#)



Switches and Lighting Controls, Industrial Grade, Disconnect
Switches, Replacement Switch, Three Pole, 60A 600V AC, Screw
Terminals, Gray

Features

- Industrial Grade
- Disconnect Switches
- Replacement Switch
- Three Pole

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstand 3,000V AC
- Electrical - Max Working Voltage - 600V AC RMS
- Environmental - Flammability - UL94-5VA and V-0 classification
- Environmental - Ingress Protection - IP67 Suitability
- Environmental - Operating Temperatures - Max Continuous- 75 °C, Minimum -40 ° w/o Impact
- Mechanical - Impact Resistance - In accordance with UL746C
- Mechanical - Product Identification - Identification and ratings are a part of the external label and molded into the receptacle mount.
- Mechanical - Terminal Identification - Terminals identified in accordance with North American and International conventions

General

Catalog Number	HBLDS60100RS
EU RoHS Indicator	No
Ingress Protection	IP67
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact

Series

Specifications

Non-Fused;Fused

- Assembly Screws - Stainless Steel
- Gaskets - Neoprene
- Hinge Spring - Stainless Steel
- Interlock Items - Replacement Parts

Style

Type

UPC

Replacement Switches

Accessories

783585955216

Electrical Ratings

Amperage Rating	60/100 A
Current / Amperage Rating	60/100 A
Dielectric Strength	Withstands 3000V AC minimum

Certifications And Compliance

Industry Standard(s)	UL Listed
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2024](#)

[Specifications - HBLDS60100RS](#)

[Warranty - Industrial & Commercial Products](#)