

IEC Pin and Sleeve Devices, Industrial Grade, Female, Receptacle, 32A 220-415V, 4-Pole 5- Wire Grounding, Terminal Screws, Red, Watertight

By Hubbell Wiring Device-Kellems
Catalog # [HBL532R6W](#)

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female, Receptacle, 32A 220-415V, 4-Pole 5- Wire Grounding, Terminal Screws, Red, Watertight



Application

High Ampacity Watertight Connections

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - 3000V AC
- Electrical - Max. Working Voltage - 600V RMS
- Electrical - Temperature Rise - Max. 30°C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of 75%
- Environmental - Flammability - HB or better per UL 94 or CSA C22.2 No. 0.17
- Environmental - Ingress Protection - IP67 Suitability
- Environmental - Moisture Resistance - Watertight per IEC 60309-1
- Environmental - Operating Temperatures - Maximum Continuous 75°C
- Minimum - 40°C w/o impact
- Mechanical - Impact Resistance - Per CSA C22.2 No.182.1 /UL1682
- Mechanical - Product Identification - Identification and ratings are a permanent part of the device housing
- Mechanical - Terminal Identification - Terminals identified in accordance with North American and IEC conventions

General

| | |
|------------------------------|--|
| Catalog Number | HBL532R6W |
| Color | Red |
| EU RoHS Indicator | Yes |
| Environmental Conditions | Watertight |
| Item Type | Single Flanged |
| Material | Thermoplastic |
| Material - Mounting Hardware | Screw Mounting |
| Number Of Poles | 4-Pole |
| Series | HBL Heavy Duty |
| Specifications | <ul style="list-style-type: none"> • Cover - Reinforced Thermoplastic Polyester |

- Cover Screw - Nickel-plated brass
- Gaskets - Solid Neoprene
- Housing - Zytel® 101 Nylon
- Mounting Flange - Zytel® 101 Nylon

Style
Type
UPC

Standard Service
Watertight Receptacle
783585405599

Dimensions

Display Size Standard Sized Product

Electrical Ratings

| | |
|----------------------------|--|
| Amperage Rating | 32 A |
| Connectivity | Pressure Terminal Screws |
| Current / Amperage Rating | 32 A |
| Current Rating | 32 A |
| Phase | Three Phase |
| Voltage Rating | <ul style="list-style-type: none"> • 220/380 V V • 240/415 V V |
| Voltage Rating Description | 220/380 V;240/415 V |
| Wattage | 13280 |

Conductor Related

| | |
|-----------------|-------------------|
| Number Of Wires | 5-Wire |
| Wire Size | #12 AWG to #8 AWG |

Certifications And Compliance

| | |
|----------------------|---|
| Industry Standard(s) | <ul style="list-style-type: none"> • CSA Standard C22.2 No. 182.1 • UL Classified to IEC 60309-1 IEC 60309-2 • UL Listed, File E146032 |
| Nema Rating | Non-NEMA |

Logistics

| | |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|



A Hubbell brand