

Interlocked Hazardous Location Receptacle, 60A 600V AC, 4-Pole 3-Wire Grounding

By Hubbell Wiring Device-Kellems
Catalog # [HBLVSQ6034](#)



Interlocked Hazardous Location Receptacle, 60A 600V AC, 4-Pole 3-Wire Grounding

Features

- Enclosures: Copper-free aluminum (less than 4/10 of 1% copper content)
- Cover Bolts: 316 Stainless Steel
- Finish: Grey Powder Polyester painted exterior, electrostatically applied
- Ratings: 600V AC, 230V DC 30-100 Amp
- Optional to include up to one (1) N/O "Break Before Main Break" auxiliary contact

General

Catalog Number	HBLVSQ6034
EU RoHS Indicator	No
Environmental Conditions	Classified Hazardous
Item Type	Unfused Mechanical Interlock Receptacle
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Series	Mechanical Interlock
Style	Non-Fused UL 1686
Type	3-Wire 4-Pole
UPC	783585242682

Dimensions

Display Size

Standard Sized Product

Electrical Ratings

Amperage Rating	60 A
Connectivity	Screw Terminals
Current / Amperage Rating	60 A
Current Rating	60 A
Phase	Single Phase
Voltage Rating Description	600 VAC
Wattage	36000

Conductor Related

Wire Size	#8 AWG to #2 AWG Copper Wire Only
-----------	-----------------------------------

Certifications And Compliance

Nema Rating	Non-NEMA
Standards - RoHS Compliance Status	CM

Product Assets

[Catalogs - WDK Catalog Full 2024](#)

[Specifications - HBLVSQ6034](#)

[Warranty - Industrial & Commercial Products](#)