

Straight Blade Devices, Receptacles, Weather-Resistant Single, Industrial Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Brown, Single Pack

By Hubbell Wiring Device-Kellems
Catalog # [HBL5361WR](#)

Straight Blade Devices, Receptacles, Weather-Resistant Single,
Industrial Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R,
Brown, Single Pack.

Application

Extra Heavy Duty Specification Grade

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - Top: UL 94V-2, Base: UL 94V-0
- Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #12-#10 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	HBL5361WR
Color	Brown
EU RoHS Indicator	No
Environmental Conditions	Weather Resistant
Horsepower - Maximum	1
Item Type	Single
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Extra Heavy Duty
Specifications	<ul style="list-style-type: none">• Auto Self-grounding Clip - Stainless steel• Base - PBT• Face - Nylon• Ground Contact - Brass• Mounting Screws - Zinc plated steel



Style
Type
UPC

- Mounting Strap - .050" (1.3) Brass
 - Power Contacts - .037 in. (.9) Brass
- Finder Groove Face
Single Receptacle
783585320632

Dimensions

Dimensions	3.28 in x 1.63 in x 1.19 in
Display Size	Standard Sized Product
Height	1.19 in
Length	3.28 in
Weight	0.2 lb
Width	1.63 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V
Wattage	2500 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#12 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Certified to CSA 22.2, No. 42 File 285• Fed. Spec. W-C-602• NEMA® WD-6 Compliant
----------------------	--

- UL Listed to UL498 File No. E2186

Nema Rating

5-20R

Logistics

Carton Quantity

10

Product Assets

[Catalogs - WDK Catalog Full 2024](#)

[Literature - EdgeConnect™ Technology FAQ](#)

[Specifications - HBL5361WR](#)

[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL5361WR-SPEC-EN | REV 10/2024