

# Straight Blade Devices, Receptacles, Weather-Resistant Duplex, Industrial Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, White, Single Pack

By Hubbell Wiring Device-Kellems  
Catalog # [HBL5362WWR](#)



Straight Blade Devices, Receptacles, Weather-Resistant Duplex,  
Industrial Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R,  
White, Single Pack.

## Application

Extra Heavy Duty Specification Grade

## Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - Top: UL 94V-2, Base: UL 94V-0
- Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #12-#10 AWG stranded or solid copper wire only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

## General

Catalog Number	HBL5362WWR
Color	White
EU RoHS Indicator	No
Environmental Conditions	Weather Resistant
Horsepower - Maximum	1
Item Type	Traditional Duplex
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Extra Heavy Duty
Specifications	<ul style="list-style-type: none"><li>• Automatic Self-grounding Clip - Stainless steel</li><li>• Base - PBT</li><li>• By-Pass Power Contacts - .036" (.9) Brass</li><li>• Clamp - Brass</li><li>• Contacts - 0.031" (0.8) Brass</li><li>• Face - Nylon</li></ul>

Style  
Type  
UPC

- Mounting Screws - Stainless Steel
  - Terminal Screws - Brass
- Finder Groove Face  
Weather Resistant  
783585320595

## Dimensions

Dimensions	3.28 in x 1.65 in x 1.19 in
Display Size	Standard Sized Product
Height	1.19 in
Length	3.28 in
Weight	0.25 lb
Width	1.65 in

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V
Wattage	2500 W

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#12 AWG to #10 AWG

## Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• Certified to CSA 22.2, No. 42 File 285</li><li>• Fed. Spec. WC596</li><li>• NEMA® WD-6 Compliant</li></ul>
----------------------	--

• UL Listed to UL498 File No.  
E2186

Nema Rating 5-20R  
Standards - RoHS Compliance Status CM

**Logistics**

Carton Quantity 10

Pallet Quantity 4500

**Product Assets**

[Catalogs - WDK Catalog Full 2024](#)  
[Literature - EdgeConnect™ Technology FAQ](#)  
[Specifications - HBL5362WWR](#)  
[Warranty - Industrial & Commercial Products](#)

