

Straight Blade Devices, Female Connector Body, Valise Series, Industrial/Commercial Grade, Straight, 2-Pole 3- Wire Grounding, 20A 125V, 5-20R

By Hubbell Wiring Device-Kellems
Catalog # [HBL5369VBK](#)

Straight Blade Devices, Female Connector Body, Valise Series, Industrial/Commercial Grade, Straight, 2-Pole 3- Wire Grounding, 20A 125V, 5-20R, Black, Single Pack.

Application

Industrial/Commercial

Performance

- Electrical:Current Interrupting: Certified for current interrupting at full rated current
- Dielectric Voltage: Withstands 2,000V minimum
- Mechanical :Terminal Accommodation #18-#12 AWG stranded copper wire only
- Terminal Identification: Terminals identified in accordance with UL 498 and CSA
- Environmental :Flammability: UL 94 HB or better
- IP Suitability: IP20
- Operating Temperatures: Maximum continuous 75°C
- minimum -40°C (w/o impact)

General

Catalog Number	HBL5369VBK
Color	Black
Cord Range	0.300"-0.660" (7.6-16.8)
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	1
Insulation	Insulated Body
Item Type	Valise
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Valise®
Specifications	<ul style="list-style-type: none"> • Assembly Screws - Plated Steel • Assembly Screws - Plated steel • Cable Inserts - PPO • Contacts - Brass



Style	Standard
Temperature Rating	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Type	Connector Body
UPC	783585019307

Dimensions

Display Size	Standard
Weight	0.15 lb

Electrical Ratings

Amperage Rating	20 A
Connectivity	Screw Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V

Conductor Related

Conductor Range	#18 AWG to #12 AWG
Number Of Wires	3-Wire
Number of Conductors	3-Wire
Wire Size	#18 AWG to #12 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • CSA Certified to C22.2 No. 42 File 280C • NEMA® WD-6 Compliant • UL Listed to UL498 File E1706
----------------------	--

Nema Rating 5-20R
Standards - RoHS Compliance CM
Status

Logistics

Carton Quantity 10

Product Assets

[Catalogs - WDK Catalog Full 2024](#)

[Specifications - HBL5369VBK](#)

[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL5369VBK-SPEC-EN | REV 10/2024