



# Straight Blade Devices, Male Inlets, Flanged, Industrial/Commercial, 20A 125V, 2-Pole 3-Wire Grounding, 5- 20P, White, Single Pack

By Hubbell Wiring Device-Kellems  
 Catalog # [HBL5378C](#)



Straight Blade Devices, Male Inlets, Flanged, Industrial/Commercial, 20A 125V, 2-Pole 3-Wire Grounding, 5-20P, White, Single Pack.

## Features

- Impact resistant thermoplastic construction
- Backwired terminations for ease of installation
- #8-32 Multiple drive terminal screws
- Mounting screws included

## Application

Extra Heavy Duty Industrial

## General

Color	<ul style="list-style-type: none"> <li>• White</li> <li>• Blanc</li> </ul>
Cord Range	0.230"-0.720" (5.8-18.3)
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	0.50
Insulation	Insulated Body
Item Type	Standard Single
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> <li>• Electrical - Current Interrupting - Certified for current interrupting at full rated current</li> <li>• Electrical - Dielectric Voltage - Withstands 2,000V minimum</li> <li>• Environmental - Flammability - UL 94 V-2</li> <li>• Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)</li> <li>• Mechanical - Product Identification - Ratings are a permanent part of the device</li> </ul>

## Dimensions

Dimensions	1.71 in x 1.69 in x 1.71 in
Display Size	Standard Sized Product
Height	1.71 in
Length	1.71 in
Weight	0.1 lb
Width	1.69 in

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Back Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V
Wattage	2500 W

## Conductor Related

Conductor Range	#18 AWG to #10 AWG
Number Of Conductors	3-Wire
Number Of Wires	3-Wire
Wire Size	#18 AWG to #10 AWG

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• Certified to CSA, C22.2, No. 42</li> <li>• NEMA® WD-6 Compliant</li> <li>• UL Listed, File E2186</li> </ul>
Nema Rating	5-20P
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalogs - WDK Catalog Full 2023](#)  
[Warranty - Industrial & Commercial Products](#)

- Mechanical - Terminal Accommodation - #18-#10 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

Series	Extra Heavy Duty
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	<ul style="list-style-type: none"><li>• Flanged Inlet</li><li>• Flanged Inlet</li></ul>
UPC	783585174402



**A proud member of the Hubbell Family.**

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_MX-HBL5378C-SPEC-EN | REV 1/2024