

**HUBBELL**  
Wiring Device-Kellems

**IEC Pin and Sleeve Devices,  
Industrial Grade, Female,  
Receptacle, 63A 220-415V, 4-Pole  
5- Wire Grounding, Terminal  
Screws, Red, Watertight**

By Hubbell Wiring Device-Kellems  
Catalog # [HBL563R6W](#)

Heavy Duty IEC Pin and Sleeve Industrial Grade Female  
Receptacle, 63A 220-415V, 4-Pole 5-Wire Grounding, Terminal  
Screws, Watertight



## Application

High Ampacity Watertight Connections

## Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstand 3000V AC
- Electrical - Max. Working Voltage - 600V RMS
- Environmental - Flammability - HB or better per UL 94 or CSA C22.2 No. 0.17
- Environmental - Ingress Protection - IP67 Suitability
- Environmental - Moisture Resistance - Watertight per IEC 60309-1
- Environmental - Operating Temperatures - Maximum Continuous 75°C
- Minimum - 40°C w/o impact
- Mechanical - Impact Resistance - Per CSA C22.2 No. 182.1 / UL1682
- Mechanical - Product Identification - Ratings are a permanent part of the device housing
- Mechanical - Terminal Identification - Terminals identified in accordance with North American and IEC conventions

## General

Catalog Number	HBL563R6W
Color	Red
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Item Type	Single Flanged
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	4-Pole
Series	HBL Heavy Duty
Specifications	<ul style="list-style-type: none"><li>• Cover - Reinforced Thermoplastic Polyester</li><li>• Cover Screw - Nickel-plated brass</li><li>• Gaskets - Solid Neoprene</li></ul>

- Housing - Zytel® 101 Nylon
- Mounting Flange - Zytel® 101 Nylon

Style	Standard Service
Type	Watertight Receptacle
UPC	783585405797

## Dimensions

Display Size	Standard Sized Product
--------------	------------------------

## Electrical Ratings

Amperage Rating	63 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	63 A
Current Rating	63 A
Phase	Three Phase
Voltage Rating	<ul style="list-style-type: none"><li>• 220/380 V V V</li><li>• 240/415 V V V</li></ul>
Voltage Rating Description	220/380 V;240/415 V
Wattage	26145

## Conductor Related

Number Of Wires	5-Wire
Wire Size	#8 AWG to #2 AWG

## Certifications And Compliance

Industry Standard(s)	Listed To Standard UL1682
Nema Rating	Non-NEMA

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - HBL563R6W](#)  
[Warranty - Industrial & Commercial Products](#)