

## Straight Blade Devices

### 20A, 125V, 2 Pole, 3 Wire Grounding

# Hubbell-PRO Heavy Duty Hospital Grade Receptacles

# HUBBELL

## Features

- Tamper-resistant shutter complies with national electrical code requirements
- Green LED Power Indicators to identify emergency circuits
- Triple wipe contacts
- High impact resistant face with circuit I.D. marking area
- Steel mounting strap

## Ordering Information

| Description  | Device Color | UPC          | Catalog Number |
|--|--------------|--------------|----------------|
| Hospital grade, tamper-resistant with power indicating LED | White        | 783585196763 | 8300WLTRA      |

## Standards

UL Listed to UL498 File No. E2186  
Certified to CSA, C22.2, No. 42 File 285  
Fed. Spec. W-C-596  
NEMA® WD-6 Compliant

## Specifications

|                                 |                   |
|---------------------------------|-------------------|
| Face                            | Nylon             |
| Base                            | PBT               |
| Power Contacts                  | Brass             |
| Ground Contacts                 | Brass             |
| Clamping Plate                  | Plated steel      |
| Mounting Strap                  | Galvanized steel  |
| Automatic Self-grounding Staple | Stainless steel   |
| Mounting Screws                 | Zinc plated steel |

## Performance

| Electrical           |  |
|----------------------|--|
| Current Interrupting | Certified for current interrupting at full rated current |


|                    |                           |
|--------------------|---------------------------|
| Dielectric Voltage | Withstands 2,000V minimum |
|--------------------|---------------------------|

### Mechanical

|                         |  |
|-------------------------|--|
| Product Identification  | Ratings are a permanent part of the device             |
| Terminal Accommodation  | #12-10 AWG stranded or solid copper wire only.         |
| Terminal Identification | Terminals identified in accordance with UL 498 and CSA |

### Environmental

|                       |   |
|-----------------------|---|
| Flammability          | UL 94V-2  |
| Operating Temperature | Maximum continuous 75°C; minimum -40°C (w/o impact) |



## Accessories

Wallplate or Weatherproof Cover

Duplex Opening

## Online Resources

eCatalog

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

