

Straight Blade Male Plug, Insulgrip Heavy Duty, Industrial/Commercial, 2-Pole 3- Wire Grounding, 15A 250V, 6-15P, Yellow, Single Pack



By Hubbell Wiring Device-Kellems
Catalog # [HBL56CM66C](#)

Straight Blade Devices, Male Plug, Insulgrip Heavy Duty, Industrial/Commercial Grade, Straight, 2-Pole 3- Wire Grounding, 15A 250V, 6-15P, Yellow, Single Pack.

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 HB or better
- Environmental - IP Suitability - IP20
- Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #18-10 AWG. Standed copper wire only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	HBL56CM66C
Color	Yellow
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Ribbed Nylon Housing Is Impact and Chemical Resistant
Horsepower - Maximum	1.5
Item Type	Insulgrip Plug
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Insulgrip®
Specifications	<ul style="list-style-type: none"> • Assembly Screws - Stainless steel • Blade Holder - Nylon • Blades - .060 in. (1.5) Nickel plated brass • Housing - Nylon • Terminal Clamp - Nickel plated steel • Terminal Retainer - Clear Polycarbonate • Terminal Screws - #8-32 Brass , multiple drive
Style	Corrosion Resistant

Type	Plug
UPC	783585013398

Dimensions

Dimensions	1.97 in x 1.53 in x 1.53 in
Height	1.53 in
Length	1.97 in
Weight	0.15 lb
Width	1.53 in

Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	250 V
Voltage Rating Description	250 V
Wattage	3750 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#18 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • CSA Certified to C22.2 No. 42 File 280 • NEMA® WD-6 Compliant • UL Listed to UL498 File E1706
Nema Rating	6-15P
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2024](#)



A Hubbell brand