

## Straight Blade Devices, Female Connector Body, Valise Series, Industrial/Commercial Grade, Straight, 2-Pole 3- Wire Grounding, 15A 125V, 5-15R

By Hubbell Wiring Device-Kellems  
Catalog # [HBL5963VY](#)

Straight Blade Devices, Female Connector Body, Valise Series, Industrial/Commercial Grade, Straight, 2-Pole 3- Wire Grounding, 15A 125V, 5-15R, Yellow, Single Pack.



### Application

Industrial/Commercial

### Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 HB or better
- Environmental - IP Suitability - IP20
- Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #18-16 AWG. Standed copper wire only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

### General

Catalog Number	HBL5963VY
Color	Yellow
Cord Range	0.230"-0.720" (5.8-18.3)
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	0.5
Insulation	Insulated Body
Item Type	Valise
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Valise®
Specifications	<ul style="list-style-type: none"> <li>• Assembly Screws - Plated Steel</li> <li>• Contacts - Brass</li> <li>• Housing - Nylon</li> </ul>
Style	Standard

Temperature Rating

Max Continuous- 75 Degrees C,  
Minimum- -40 Without Impact

Type  
UPC

Connector Body  
783585019604

### Dimensions

Display Size  
Weight

Standard  
0.1 lb

### Electrical Ratings

Amperage Rating  
Connectivity  
Current / Amperage Rating  
Current Rating  
Dielectric Strength  
Phase  
Voltage Rating  
Voltage Rating Description

15 A  
Screw Terminals  
15 A  
15 A  
Withstands 2,000V minimum  
Single Phase  
125 VAC  
125 V

### Conductor Related

Conductor Range  
Number Of Wires  
Wire Size

#14 AWG to #12 AWG  
3-Wire  
#18 AWG to #16 AWG

### Certifications And Compliance

Industry Standard(s)

- CSA Certified to C22.2 No. 42 File 280C
- NEMA® WD-6 Compliant
- UL Listed to UL498 File E1706

Nema Rating  
Standards - RoHS Compliance  
Status

5-15R  
CM

### Logistics

Carton Quantity

10



A Hubbell brand