

IEC Pin and Sleeve

60A, 3 Phase, 250V, 3 Pole, 4 Wire

Low Profile Receptacle

Features

- Compact Design
- Fully Interchangeable with IEC 60309 Devices
- Solid one-piece pins for reliable electrical contact
- Molded in durable and non conductive nylon

Ordering Information

Description	UPC	Catalog Number
IEC Pin and Sleeve Receptacle	783585507804	A460P9



Listings

UL Listed, File E146033
CSA Certified File LR280C
UL Classified to IEC 60309-1 IEC 60309-2

Specifications

Housing	PBT
Retainer	High-Impact Thermoset
Gaskets	Santoprene
Terminal Screws	Stainless Steel


Performance

Electrical
Current Interrupting Certified for current interruption at full rated current

Dielectric Voltage Withstands 3,000V AC
Max Working Voltage 250V RMS

Mechanical
Impact Resistance Per CSA C22.2 No. 182.1 / UL1682
Product Identification Ratings are a permanent part of the device housing
Terminal Identification Terminals identified in accordance with North American and IEC conventions

Environmental
Flammability VO
Ingress Protection IP 22
Operating Temperatures Max. Continuous +75°C; Min. -40°C w/o impact



Online Resources

Customer Use Drawing
eCatalog
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

HUBBELL

