



Straight Blade Devices, Female Connector Body, Valise Series, Industrial/Commercial Grade, Straight, 2-Pole 3- Wire Grounding, 15A 125V, 5-15R

By Hubbell Wiring Device-Kellems
Catalog # [HBL5969VBLK](#)

Straight Blade Devices, Female Connector Body, Valise Series, Industrial/Commercial Grade, Straight, 2-Pole 3- Wire Grounding, 15A 125V, 5-15R, Black, Single Pack.



Application

- Industrial/Commercial

General

Color	
Cord Range	0.220"-0.660" (5.6-16.8)
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	0.5
Insulation	Insulated Body
Item Type	Valise
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none">Electrical - Current Interrupting - Certified for current interrupting at full rated currentElectrical - Dielectric Voltage - Withstands 2,000V minimumEnvironmental - Flammability - UL 94 HB or betterEnvironmental - IP Suitability - IP20Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)Mechanical - Terminal Accommodation - #18-12 AWG. Standed copper wire onlyMechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

Dimensions

Dimensions	2.68 in x 1.32 in x 2.68 in
Display Size	Standard
Height	2.68 in
Length	2.68 in
Weight	0.15 lb
Width	1.32 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Conductor Range	#14 AWG to #12 AWG
Number Of Wires	3-Wire
Wire Size	#18 AWG to #12 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">CSA Certified to C22.2 No. 42 File 280CNEMA® WD-6 CompliantUL Listed to UL498 File E1706
Nema Rating	5-15R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
Pallet Quantity	8400

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Warranty - Industrial & Commercial Products](#)

Series	Valise®
Style	Standard
Temperature Rating	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Type	Connector Body
UPC	783585013275



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_MX-HBL5969VBLK-SPEC-EN | REV 5/2024