

IEC Pin and Sleeve

60A, 3 PhaseY, 120/208V, 4 Pole, 5 Wire

Angled Plug

Features

- Compact Design
- Fully Interchangeable with IEC 60309 Devices
- Solid one-piece pins for reliable electrical contact
- Molded in durable and non conductive nylon

Ordering Information

Description	UPC	Catalog Number
IEC Pin and Sleeve Angled Plug	783585008455	A560P9



Listings


UL Listed, File E146033
CSA Certified File LR280C
UL Classified to IEC 60309-1 IEC 60309-2

Specifications

Housing	PBT
Contact Carrier	High-Impact Thermoset
Terminal Screws	Stainless Steel

Performance

Electrical	
Current Interrupting	Certified for current interruption at full rated current
Dielectric Voltage	Withstands 3,000V AC
Max Working Voltage	250V RMS
Mechanical	
Impact Resistance	Per CSA C22.2 No. 182.1 / UL1682
Product Identification	Ratings are a permanent part of the device housing
Terminal Identification	Terminals identified in accordance with North American and IEC conventions
Environmental	
Flammability	VO
Ingress Protection	IP 22
Operating Temperatures	Max. Continuous +75°C; Min. -40°C w/o impact



Online Resources

Customer Use Drawing
eCatalog
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

HUBBELL

