

Straight Blade Devices, Female Connector Body, Valise Series, Industrial/Commercial Grade, Straight, 2-Pole 3- Wire Grounding, 15A 125V, 5-15R

By Hubbell Wiring Device-Kellems
Catalog # [HBL5969VY](#)

Straight Blade Devices, Female Connector Body, Valise Series, Industrial/Commercial Grade, Straight, 2-Pole 3- Wire Grounding, 15A 125V, 5-15R, Yellow, Single Pack.



Application

- Industrial/Commercial

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 HB or better
- Environmental - IP Suitability - IP20
- Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #18-12 AWG. Standed copper wire only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	HBL5969VY
Color	Jaune
Cord Range	0.230"-0.720" (5.8-18.3)
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	0.5
Insulation	Insulated Body
Item Type	Valise
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Valise®
Specifications	<ul style="list-style-type: none">• Assembly Screws - Plated Steel• Assembly Screws - Plated steel• Cable Inserts - PPO• Contacts - Brass

Style

Temperature Rating

Type

UPC

Dimensions

Dimensions	2.68 in x 1.32 in x 2.68 in
Display Size	Standard
Height	2.68 in
Length	2.68 in
Weight	0.1 lb
Width	1.32 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V

Conductor Related

Conductor Range	#14 AWG to #12 AWG
Number Of Wires	3-Wire
Wire Size	#18 AWG to #12 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• CSA Certified to C22.2 No. 42 File 280C
----------------------	---

- Housing - Nylon
 - Terminal Clamp - Nickel plated steel
 - Terminal Screws - #8-32 Brass , multiple drive
- Standard
Max Continuous- 75 Degrees C,
Minimum- -40 Without Impact
Connector Body
783585013107

- NEMA® WD-6 Compliant
- UL Listed to UL498 File E1706

Carton Quantity 10
Pallet Quantity 8400

Nema Rating 5-15R
Standards - RoHS Compliance CM
Status

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL5969VY](#)
[Warranty - Industrial & Commercial Products](#)

Logistics



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL5969VY-SPEC-EN | REV 10/2024