

Locking Devices, Twist-Lock®, Industrial, Female Connector Body, 20A 250V, 2-Pole 2-Wire Non Grounding, L2-20R, Screw Terminal, Black and White

By Hubbell Wiring Device-Kellems
Catalog # [HBL7101C](#)

Locking Devices, Twist-Lock®, Industrial, Female Insulgrip® Connector Body, 20A 250V AC, 2-Pole 2-Wire Non Grounding, NEMA L2-20R, Screw Terminal, Black and White Nylon.

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.17
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #18 AWG - #10 AWG stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

General

Catalog Number	HBL7101C
Cord Range	0.220"-0.720"(5.6-18.3)
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	20A Insulgrip® Connector
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none"> • Assembly Screws - Steel - zinc plated • Body - Nylon • Contacts - Bronze • Terminal Clamp - Cold rolled steel - nickel plated • Terminal Retainer - Clear polycarbonate • Terminal Screw - Brass
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C



Type	w/o impact, -25° with impact.
UPC	Connector Body 783585177007

Dimensions

Dimensions	1.53 in x 1.53 in x 2.78 in
Display Size	Standard
Height	2.78 in
Length	1.53 in
Weight	0.15 lb
Width	1.53 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	250 VAC
Voltage Rating Description	250 VAC

Conductor Related

Cable Range	0.230 - 0.720 in
Number Of Wires	2-Wire
Wire Size	#18 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	Fed.Spec.W-C-596
Nema Rating	L2-20P
Standards - RoHS Compliance	CM
Status	

Logistics

Carton Quantity	10
Pallet Quantity	6000

Product Assets



A Hubbell brand