

# Locking Devices, Twist-Lock®, Industrial, Male Plug, 20A 250V, 2-Pole 2-Wire Non-Grounding, L2-20P, Screw Terminal, Black and White

By Hubbell Wiring Device-Kellems  
Catalog # [HBL7102C](#)



Locking Devices, Twist-Lock®, Industrial, Male Insulgrip® Plug, 20A 250V, 2-Pole 2-Wire Non-Grounding, NEMA L2-20P, Screw Terminal, Black and White Nylon, Polarized.

## Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.17
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #16 AWG - #8 AWG stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

## General

|                              |   |
|------------------------------|---|
| Catalog Number               | HBL7102C  |
| Cord Range                   | 0.230"-0.720"(5.6-18.3)   |
| EU RoHS Indicator            | Yes   |
| Environmental Conditions     | Indoor Dry Unless Protected By Additional Means   |
| Item Type                    | 20A Male Non-Grounding Insulgrip® Plug  |
| Material                     | Nylon   |
| Material - Mounting Hardware | Cord Mounted  |
| Number Of Poles              | 2-Pole  |
| Operating Temperature        | Maximum continuous 75°C and minimum -40°C without Impact  |
| Specifications               | <ul style="list-style-type: none"> <li>• Assembly Screws - Steel - zinc plated</li> <li>• Body - Nylon</li> <li>• Contacts - Bronze</li> <li>• Terminal Clamp - Cold rolled steel - nickel plated</li> <li>• Terminal Retainer - Clear polycarbonate</li> <li>• Terminal Screw - Brass</li> </ul> |
| Type                         | Plugs   |
| UPC                          | 783585177052  |

## Dimensions

|              |                             |
|--------------|-----------------------------|
| Dimensions   | 1.53 in x 1.53 in x 1.97 in |
| Display Size | Standard Sized              |
| Height       | 1.97 in                     |
| Length       | 1.53 in                     |
| Weight       | 0.15 lb                     |
| Width        | 1.53 in                     |

## Electrical Ratings

|                            |                           |
|----------------------------|---------------------------|
| Amperage Rating            | 20 A                      |
| Connectivity               | Pressure Terminal Screws  |
| Current / Amperage Rating  | 20 A                      |
| Current Rating             | 20 A                      |
| Dielectric Strength        | Withstands 2,000V minimum |
| Phase                      | Single Phase              |
| Voltage Rating             | 250 VAC                   |
| Voltage Rating Description | 250 VAC                   |

## Conductor Related

|                 |                      |
|-----------------|----------------------|
| Cable Range     | 0.220 - 0.720 in     |
| Cord Type       | All Listed Portables |
| Number Of Wires | 2-Wire               |
| Wire Size       | #16 AWG to #8 AWG    |

## Certifications And Compliance

|                                    |   |
|------------------------------------|---|
| Industry Standard(s)               | <ul style="list-style-type: none"> <li>• Certified to CSA C22.2 No.43</li> <li>• Fed.Spec. W-C-597</li> <li>• Listed to UL 499</li> </ul> |
| Nema Rating                        | L2-20P  |
| Standards - RoHS Compliance Status | CM  |

## Logistics

|                 |      |
|-----------------|------|
| Carton Quantity | 10   |
| Pallet Quantity | 3600 |



A Hubbell brand