

Straight Blade Devices, Receptacles, Single, Industrial Grade, 4- Pole 4-Wire Non- Grounding, 60A 3 Phase 120/208V AC, 18-60R, Black, Single Pack

By Hubbell Wiring Device-Kellems
Catalog # [HBL7301A](#)

Straight Blade Devices, Receptacles, Single, Industrial Grade, 4-Pole 4-Wire Non-Grounding, 60A 3 Phase 120/208V AC, 18-60R, Black, Single Pack.



Application

- Heavy Duty

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 HB
- Environmental - IP Suitability - IP20
- Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #12 AWG through #4 AWG copper wire only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	HBL7301A
Color	Black
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	7.5
Item Type	Single
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	4-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none">• Box Terminals - Copper• Contacts - Brass• Ground Shunt - Brass• Housing - Reinforced Thermoplastic Polyester• Mounting Plate - .062 in. (1.5) Pre-Plated Steel

UPC 783585015095

Dimensions

Display Size	Standard Sized Product
Length	3.28 in
Weight	0.55 lb
Width	1.81 in

Electrical Ratings

Amperage Rating	60 A
Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	60 A
Current Rating	60 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Three Phase
Voltage Rating	120/208 VAC
Voltage Rating Description	120/208 V AC
Wattage	12480 W

Conductor Related

Number Of Wires	4-Wire
Wire Size	#12 AWG to #4 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• CSA Certified• NEMA® WD-6 Compliant• UL Listed File E2186
Nema Rating	18-60R

Logistics

Carton Quantity	5
Pallet Quantity	1860

Product Assets

[Catalogs - WDK Catalog Full 2024](#)



A Hubbell brand