

**HUBBELL**  
Wiring Device-Kellems

**Locking Devices, Twist-Lock®,  
Industrial, Receptacle, 50A 250V  
DC/ 600V AC, 3-Pole 4-Wire  
Grounding, Non-NEMA, Screw  
Terminal, Phenolic Black**

By Hubbell Wiring Device-Kellems  
Catalog # [HBL7379](#)

Locking Devices, Twist-Lock®, Industrial, Receptacle, 50A 250V  
DC/ 600V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw  
Terminal, Phenolic Black



## General

Application	
Catalog Number	HBL7379
Color	
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	50A Receptacle
Material	Phenolic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	Electrical - Current Interrupting - Certified for current interrupting at full rated current  Electrical - Dielectric Voltage - Withstands 2,000V minimum  Environmental - Flammability - UL 94 VO  Environmental - Operating Temperatures - Maximum continuous 75°C minimum - 40°C (w/o impact)  Mechanical - Terminal Accommodation - #10 AWG - #6 AWG solid or stranded copper wire only
Type	Receptacle  Receptacle
UPC	783585237176

## Dimensions

Dimensions	3.28 in x 2.12 in x 2.36 in
Height	2.36 in
Length	3.28 in
Weight	0.75 lb
Width	2.12 in

## Electrical Ratings

Amperage Rating	50 A
Connectivity	Screw Terminals
Current / Amperage Rating	50 A
Current Rating	50 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Multi Phase
Voltage Rating	250 VDC/600 VAC
Voltage Rating Description	250 VDC/600 VAC

## Conductor Related

Number Of Wires	4-Wire
Wire Size	#8 AWG to #4 AWG

## Certifications And Compliance

Industry Standard(s)	Certified to CSA C22.2 No.42  Listed to UL 498
Nema Rating	Non-NEMA

## Logistics

Carton Quantity	10
Pallet Quantity	950

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)

[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK\_MX-HBL7379-SPEC-EN | REV 6/2024