

## Locking Devices, Twist-Lock®, Industrial, Flush Receptacle, 20A 3-Phase Wye 120/208V AC, 4-Pole 4-Wire Non- Grounding, Non-NEMA, Screw Terminal, Black

By Hubbell Wiring Device-Kellems  
Catalog # [HBL7410B](#)



Locking Devices, Twist-Lock®, Industrial, Single Flush Receptacle, 20A 3-Phase Wye 120/208V AC, 4-Pole 4-Wire Non-Grounding, Non-NEMA, Screw Terminal, Back wired, Black thermoset.

### Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - V2 or better per UL94/CSA 22.2 No.0.17
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #16 AWG - #8 AWG solid or stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

### General

Catalog Number	HBL7410B
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	20A Single Flush Receptacle
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	4-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none"> <li>• Base - Glass-Reinforced thermoplastic polyester (RTP)</li> <li>• Contacts - Brass</li> <li>• Face - Nylon</li> <li>• Mounting Strap - Brass</li> <li>• Terminal Screws - #10 - 32 Brass</li> </ul>
Type	Receptacle
UPC	783585333526

### Dimensions

Dimensions	3.61 in x 1.71 in x 1.28 in
Display Size	Standard Sized Product
Height	1.28 in
Length	3.61 in
Weight	0.25 lb
Width	1.71 in

### Electrical Ratings

Amperage Rating	20 A
Connectivity	Back Wired Screw Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Three Phase
Voltage Rating	3 Phase WYE 120/208 VAC
Voltage Rating Description	3 Phase WYE 120/208 VAC

### Conductor Related

Number Of Wires	4-Wire
Wire Size	#16 AWG to #8 AWG

### Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• Certified to CSA C22.2 No.42</li> <li>• Fed.Spec. W-C-596</li> <li>• Listed to UL 498</li> </ul>
Nema Rating	Non-NEMA
Standards - RoHS Compliance Status	CM

### Logistics

Carton Quantity	10
Pallet Quantity	3780

### Product Assets

[Catalogs - WDK Catalog Full 2024](#)



A Hubbell brand