

Hubbell-PRO

16 A, 220-240 VAC, 2-POLE, 3-WIRE

Splash Proof Receptacle

HUBBELL

Features

- IP44 environmental ratings
- Impact and corrosion resistant insulated non-metallic housing
- Sequential contact engagement to prevent a momentary over-voltage
- Color coded housings provide quick identification of mating devices

Ordering Information

Description	Color	UPC	Catalog Number
Heavy Duty Products, IEC Pin and Sleeve Devices, Hubbell-PRO, Female, Receptacle	Blue	783585676906	C316R6SA

Listings

VDE, CE

Specifications

Application	High Ampacity Connections
Connection	Pressure Screw Terminal
Wire Size	#14AWG to #12AWG
Material	PBT
Mounting	Screw Mount

Performance


Electrical	Mechanical	Environmental
Dielectric Voltage	Impact Resistance	Flammability
Max. Working Voltage	Product Identification	Ingress Protection
	Terminal Identification	Moisture Resistance
		Temperature Rating

Withstand 3000V AC
600V AC RMS

Per CSA C22.2 No. 182.1 / UL1682
Identification and ratings are marked on device housing

Terminals identified in accordance with North American and IEC conventions

HB
IP44
IEC 60309-1
Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.



Complementary Products

Complementary Products

Adapter Plate, Back Box

Online Resources

Customer Sales Drawings
eCatalog
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

